

SPECIFICATIONS

WF152BD05/06/07/08 6" die cast, paper/glass fiber cone mid/woofers, 4/8 ohm



The 6" transducers WF152BD05 (round, 4 ohm), WF152BD07 (truncated, 4 ohm), WF152BD06 (round, 8 ohm), and WF152BD08 (truncated, 8 ohm) were designed as high performance bass and midrange units for compact monitors and high-end hi-fi speakers.

FEATURES

- Balanced Drive motor structure for optimal drive force symmetry resulting in largely reduced even order harmonic distortion
- Copper cap on center pole to reduce voice coil inductance and to minimize variations in voice coil inductance as a function of voice coil position
- Cone made of a new paper/glass fiber mix with improved consistency and
- Rigid die cast alu chassis with extensive venting for lower air flow speed reducing audible distortion
- · Vented voice coil former for reduced distortion and compression
- Vented center pole with dual flares for reduced noise level at large cone excursions
- Heavy-duty black fiber glass voice coil former to reduce mechanical losses resulting in better dynamic performance and low-level details
- Large motor with 1¼" voice coil diameter for better control and power handling
- Built-in alu field-stabilizing ring for reduced distortion at high levels
- Low-loss suspension (high Qm) for better reproduction of details and dynamics
- Black motor parts for better heat transfer to the surrounding air
- · Conex spider for better durability under extreme conditions
- Gold plated terminals to ensure long-term trouble free connection



Left photo: Round frame version. Right: Truncated frame version

NOMINAL SPECIFICATIONS

Notes	Parameter	WF152BD05/07		WF152BD06/08		
		Before burn-in	After burn-in	Before burn-in	After burn-in	Unit
	Nominal size		6		6	[inch.]
	Nominal impedance		4 8			[ohm]
	Recommended max. upper frequency limit	-	3 3			[kHz]
1, 4	Sensitivity, 2.83V/1m (average SPL in range 300 - 1,000 Hz)	90		87		[dB]
2, 4	Power handling, short term, IEC 268-5, no additional filtering					[W]
2, 4	Power handling, long term, IEC 268-5, no additional filtering					[W]
2, 4	Power handling, continuous, IEC 268-5, no additional filtering	70		70		[W]
	Effective radiating area, Sd	93		93		[cm²]
3, 4, 6	Resonance frequency (free air, no baffle), F _S	50	44.5	51.5	46	[Hz]
3, 4, 0	Moving mass, incl. air (free air, no baffle), Mms	13	3.5	12	2.8	[g]
3, 4	Force factor, Bxl	6.35		8.0		[N/A]
3, 4, 6	Suspension compliance, C _{ms}	0.75	0.94	0.75	0.94	[mm/N]
3, 4, 6	Equivalent air volume, Vas	9.2	11.5	9.2	11.5	[lit.]
3, 4, 6	Mechanical resistance, Rms	0.41	0.46	0.41	0.46	[Ns/m]
3, 4, 6	Mechanical Q, Q _{ms}	10.3	8.2	10.1	8.0	[-]
3, 4, 6	Electrical Q, Qes	0.34	0.30	0.41	0.36	[-]
3, 4, 6	Total Q, Qts	0.33	0.29	0.39	0.35	[-]
4	Voice coil resistance, RDC	3.2		6.3		[ohm]
5	Voice coil inductance, Le (measured at 10 kHz)	0.11		0.19		[mH]
	Voice coil inside diameter	32		32		[mm]
	Voice coil winding height	14		14		[mm]
	Air gap height	5		5		[mm]
	Theoretical linear motor stroke, Xmax	±4.5		±4.5		[mm]
	Magnet weight	550		550		[g]
	Total unit net weight excl. packaging	1.44		1.44		[kg]
3, 4, 5	K _{rm}	51		74		[mohm]
3, 4, 5	E _{rm}	0.40		0.41		[-]
3, 4, 5	K _{xm}	114		195		[mH]
3, 4, 5	Exm	0.29		0.28		[-]

Note 1 Measured in infinite baffle.

Note 2 Tested in free air (no cabinet).

Note 3 Measured using a semi-constant current source, nominal level 2 mA.

Note 4 Measured at 25 deg. C

Note 5 It is generally a rough simplification to assume that loudspeaker transducer voice coils exhibit the characteristics of an inductor. Instead it is a far more accurate approach to use the more advanced model often referred to as the "Wright empirical model", also used in LEAP-4 as the TSL model (www.linearx.com), involving parameters K_{FM}, E_{FM}, K_{XM}, and E_{XM}. This more accurate transducer model is described in a technical paper here at our web site.

Note 6 After burn-in specifications are measured 12 hours after exciting the transducer by a 20 Hz sine wave for 2 hours at level 10/14.1 V_{RMS} (4/8 ohm version). The unit is not burned in before shipping.


Specifications are subject to change without any further notice. Copyright © 2018 by Wavecor Ltd., Guangzhou, China. All rights reserved. Wavecor® is a registered trademark of Wavecor Ltd. For more information please visit **www.Wavecor.com**



SPECIFICATIONS


WF152BD05/06/07/08 6" die cast, paper/glass fiber cone mid/woofers, 4/8 ohm





Measuring conditions, SPL
Driver mounting: Flush in infinite
baffle, back side open (no cabinet)
Microphone distance: 1.0 m
Input level: 2.83 V_{RMS}
Smoothing: 1/6 oct.

Measuring conditions, impedance Driver mounting: Free air, no baffle, back side open (no cabinet) Input signal: Semi-current-drive, nominal current 2 mA Smoothing: None



Specifications are subject to change without any further notice. Copyright © 2018 by Wavecor Ltd., Guangzhou, China. All rights reserved. Wavecor® is a registered trademark of Wavecor Ltd. For more information please visit **www.Wavecor.com**





SPECIFICATIONS

WF152BD05/06/07/08 6" die cast, paper/glass fiber cone mid/woofers, 4/8 ohm




OUTLINE DRAWING (nominal dimensions, mm)






Truncated dimension (other dimensions as round version)



CONNECTIONS



Thickness, both terminals: 0.5 mm Terminal plating: Gold

PACKAGING AND ORDERING INFORMATION

Part no. WF152BD05-01	4 ohm version, round, individual packaging (one piece per box)
Part no. WF152BD05-02	4 ohm version, round, bulk packaging
Part no. WF152BD06-01	8 ohm version, round, individual packaging (one piece per box)
Part no. WF152BD06-02	8 ohm version, round, bulk packaging
Part no. WF152BD07-01	4 ohm version, truncated, individual packaging (one piece per box)
Part no. WF152BD07-02	4 ohm version, truncated, bulk packaging
Part no. WF152BD08-01	8 ohm version, truncated, individual packaging (one piece per box)
Part no. WF152BD08-02	8 ohm version, truncated, bulk packaging

Latest update: September 19, 2018

Specifications are subject to change without any further notice. Copyright © 2018 by Wavecor Ltd., Guangzhou, China. All rights reserved. Wavecor® is a registered trademark of Wavecor Ltd. For more information please visit **www.Wavecor.com**